



PRODUCT-DETAILS

# ACS550-U1-023A-4+B055

ACS550-U1-023A-

4+B055,15HP/23AMPS,15HP,380-500V +-

10%,IP54-NEMA12,R2,48-63Hz,Dir

Connect,Bot/Side Conduit

## General Information

Global Commercial Alias	ACS550-U1-023A-4+B055
Product ID	3AUA0000004237
ABB Type Designation	ACS550-U1-023A-4+B055
EAN	6438177206545
Catalog Description	ACS550-U1-023A-4+B055,15HP/23AMPS,15HP,380-500V +-10%,IP54-NEMA12,R2,48-63Hz,Dir Connect,Bot/Side Conduit
Long Description	ACS550-U1-023A-4+B055

## Ordering

Core Credit	0.00
Country of Origin	United States (US)
Customs Tariff Number	85044080
Invoice Description	ACS550-U1-023A-4+B055,15HP/23AMPS,15HP,380-500V +-10%,IP54-NEMA12,R2,48-63Hz,Dir Connect,Bot/Side Conduit
Made To Order	No
Minimum Order Quantity	1 EA
Order Multiple	1 EA
Quote Only	No
Selling Unit of Measure	each

## Dimensions

Product Net Weight	0 kg
--------------------	------

## Technical

Number of Phases	3
Frequency (f)	48...63 Hz
Frame Size	R2
Input Voltage (U <sub>in</sub> )	380...500+-10% V

Additional Information	
Product Main Type	ACS550-U1
Product Name	-

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories
Drives → Low Voltage AC Drives → Legacy AC Drives → ACS550-U1 - Wall-mounted base drive US