

## PRODUCT-DETAILS

# ACH550-01-044A-4+B055

## ACH550 ACH550-01-044A-4+B055 Pn 22kW, I2n 44A IP54



### General Information

Global Commercial Alias	ACH550-01-044A-4+B055
Product ID	3AUA0000004384
ABB Type Designation	ACH550-01-044A-4+B055
EAN	6410038055714
Catalog Description	ACH550 ACH550-01-044A-4+B055 Pn 22kW, I2n 44A IP54

### Electrical Data

Temp Class	Freq	Voltage	Power	Current
--	50/60 Hz	380-480 V	22.00 kW	44.00 A

### Ordering

Country of Origin	China (CN) Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACH550 ACH550-01-044A-4+B055 Pn 22kW, I2n 44A IP54
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure piece

Dimensions

Product Net Weight	25.8 kg
Product Net Depth / Length	306 mm
Product Net Height	723 mm
Product Net Width	257 mm

Technical

Number of Phases	3
Frequency (f)	48 ... 63 Hz
Frame Size	R4
Input Voltage (U <sub>in</sub> )	380 ... 480 V
Mounting Type	Wall Mounting
Output Current, Normal Use (I <sub>n</sub> )	44 A
Output Power, Normal Use (P <sub>n</sub> )	22 kW

Additional Information

Product Main Type	ACH550
Product Name	Frequency converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

Categories

Drives → Low Voltage AC Drives → Legacy AC Drives → ACH550-01 - Wall-mounted drive for HVAC

