



## PRODUCT-DETAILS

# ACS550-U1-02A7-6+B055

## ACS550-U1-02A7-

## 6+B055,2HP/2.7AMPS,2HP,,IP54-

## NEMA12,R2,48-63Hz,Dir Connect,Bot/Side

### Conduit

#### General Information

Global Commercial Alias	ACS550-U1-02A7-6+B055
Product ID	3AUA0000009460
ABB Type Designation	ACS550-U1-02A7-6+B055
EAN	6438177178057
Catalog Description	ACS550-U1-02A7-6+B055,2HP/2.7AMPS,2HP,,IP54-NEMA12,R2,48-63Hz,Dir Connect,Bot/Side Conduit
Long Description	ACS550-U1-02A7-6+B055

#### Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Invoice Description	ACS550-U1-02A7-6+B055,2HP/2.7AMPS,2HP,,IP54-NEMA12,R2,48-63Hz,Dir Connect,Bot/Side Conduit
Made To Order	No
Minimum Order Quantity	1 EA
Order Multiple	1 EA
Quote Only	No
Selling Unit of Measure	each

#### Dimensions

Product Net Weight	0 kg
--------------------	------

#### Technical

Frame Size	R2
------------	----

#### Additional Information

Product Main Type	ACS550-U1
Product Name	-

---

## Categories

---

Drives → Low Voltage AC Drives → Legacy AC Drives → ACS550-U1 - Wall-mounted base drive US