



PRODUCT-DETAILS

ACS550-U1-052A-6+B055

ACS550-U1-052A-6+B055,50HP/52AMPS,50HP,,IP54-NEMA12,R4,48-63Hz,Dir Connect,Bot/Side

Conduit

General Information

Global Commercial Alias	ACS550-U1-052A-6+B055
Product ID	3AUA0000009479
ABB Type Designation	ACS550-U1-052A-6+B055
EAN	6438177177906
Catalog Description	ACS550-U1-052A-6+B055,50HP/52AMPS,50HP,,IP54-NEMA12,R4,48-63Hz,Dir Connect,Bot/Side Conduit
Long Description	ACS550-U1-052A-6+B055

Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Invoice Description	ACS550-U1-052A-6+B055,50HP/52AMPS,50HP,,IP54-NEMA12,R4,48-63Hz,Dir Connect,Bot/Side Conduit
Made To Order	No
Minimum Order Quantity	1 EA
Order Multiple	1 EA
Quote Only	No
Selling Unit of Measure	each

Dimensions

Product Net Weight	0 kg
--------------------	------

Technical

Frame Size	R4
------------	----

Additional Information

Product Main Type	ACS550-U1
Product Name	-

Categories

Drives → Low Voltage AC Drives → Legacy AC Drives → ACS550-U1 - Wall-mounted base drive US