



PRODUCT-DETAILS

ACS550-U1-125A-6

ACS550-U1-125A-

6,125HP/125AMPS,125HP,,IP21-NEMA1,R6,48-63Hz,Dir Connect,Bot/Side Conduit

General Information

Global Commercial Alias	ACS550-U1-125A-6
Product ID	3AUA0000009582
ABB Type Designation	ACS550-U1-125A-6
EAN	6438177176985
Catalog Description	ACS550-U1-125A-6,125HP/125AMPS,125HP,,IP21-NEMA1,R6,48-63Hz,Dir Connect,Bot/Side Conduit
Long Description	ACS550-U1-125A-6

Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Invoice Description	ACS550-U1-125A-6,125HP/125AMPS,125HP,,IP21-NEMA1,R6,48-63Hz,Dir Connect,Bot/Side Conduit
Made To Order	No
Minimum Order Quantity	1 EA
Order Multiple	1 EA
Quote Only	No
Selling Unit of Measure	each

Dimensions

Product Net Weight	0 kg
--------------------	------

Technical

Frame Size	R6
------------	----

Additional Information

Product Main Type	ACS550-U1
Product Name	-

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	-------------------------------------------------------------

Categories

Drives → Low Voltage AC Drives → Legacy AC Drives → ACS550-U1 - Wall-mounted base drive US