

PRODUCT-DETAILS

ACS800-01-0205-5

ACS800-01-0205-5 Pcont.max:160kW,
Icont.max:260A



General Information

Global Commercial Alias	ACS800-01-0205-5
Product ID	3AUA0000015039
ABB Type Designation	ACS800-01-0205-5
Catalog Description	ACS800-01-0205-5 Pcont.max:160kW, Icont.max:260A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACS800-01-0205-5 Pcont.max:160kW, Icont.max:260A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	67 kg
Product Net Depth /	399 mm

Length	
Product Net Height	880 mm
Product Net Width	300 mm

Technical	
Number of Phases	3
Frequency (f)	48 ... 63 Hz
Frame Size	R6
Input Voltage (U _{in})	380 ... 500 V
Mounting Type	Wall-mounting
Output Current, Heavy-Duty Use (I _{HD})	215 A
Output Current, Light-Overload Use (I _{LD})	254 A
Output Current, Normal Use (I _n)	260 A
Output Power, Heavy-Duty Use (P _{HD})	132 kW
Output Power, Light-Overload Use (P _{LD})	160 kW
Output Power, Normal Use (P _n)	160 kW

Additional Information	
Product Main Type	ACS800-01-0205-5
Product Name	Frequency Converter

Classifications	
UNSPSC	39122001

Environmental	
SCIP	9137de42-9806-4708-a144-33d9e4e244e2 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Legacy AC Drives → ACS800 single drives → ACS800-01 - Wall-mounted 6-pulse drive

