

PRODUCT-DETAILS

ACS800-01-0145-7

ACS800-01-0145-7 Pcont.max:132kW, Icont.max:134A



General Information

Global Commercial Alias	ACS800-01-0145-7
Product ID	3AUA0000015040
ABB Type Designation	ACS800-01-0145-7
Catalog Description	ACS800-01-0145-7 Pcont.max:132kW, Icont.max:134A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACS800-01-0145-7 Pcont.max:132kW, Icont.max:134A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	67 kg
Product Net Depth / Length	399 mm
Product Net Height	880 mm

Product Net Width	300 mm
-------------------	--------

Technical

Number of Phases	3
Frequency (f)	48 ... 63 Hz
Frame Size	R6
Input Voltage (U_{in})	525 ... 690 V
Mounting Type	Wall-mounting
Output Current, Heavy-Duty Use (I_{HD})	95 A
Output Current, Light-Overload Use (I_{LD})	125 A
Output Current, Normal Use (I_n)	134 A
Output Power, Heavy-Duty Use (P_{HD})	90 kW
Output Power, Light-Overload Use (P_{LD})	110 kW
Output Power, Normal Use (P_n)	132 kW

Additional Information

Product Main Type	ACS800-01-0145-7
Product Name	Frequency Converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	9137de42-9806-4708-a144-33d9e4e244e2 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Legacy AC Drives → ACS800 single drives → ACS800-01 - Wall-mounted 6-pulse drive

