

PRODUCT-DETAILS

ACS800-04-0205-5

ACS800-04-0205-5 P_{cont.max}:160kW, I_{cont.max}:260A



General Information

Global Commercial Alias	ACS800-04-0205-5
Product ID	3AUA0000015089
ABB Type Designation	ACS800-04-0205-5
Catalog Description	ACS800-04-0205-5 P _{cont.max} :160kW, I _{cont.max} :260A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACS800-04-0205-5 P _{cont.max} :160kW, I _{cont.max} :260A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	64 kg
Product Net Depth / Length	399 mm
Product Net Height	700 mm

Product Net Width	300 mm
-------------------	--------

Technical

Number of Phases	3
Frequency (f)	48 ... 63 Hz
Frame Size	R6
Input Voltage (U _{in})	380 ... 500 V
Mounting Type	Module for cabinet assembly
Output Current, Heavy-Duty Use (I _{HD})	215 A
Output Current, Light-Overload Use (I _{LD})	254 A
Output Current, Normal Use (I _n)	260 A
Output Power, Heavy-Duty Use (P _{HD})	132 kW
Output Power, Light-Overload Use (P _{LD})	160 kW
Output Power, Normal Use (P _n)	160 kW

Additional Information

Product Main Type	ACS800-04-0205-5
Product Name	Frequency Converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	e550f262-cea9-43a6-bbb7-76ebc5b9dc70 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Legacy AC Drives → ACS800 drive modules → ACS800-04 - Single drive module

