



## PRODUCT-DETAILS

# ACS800-U1-0175-7

ACS800-U1-0175-7; ACS800-U1-0175-7

Pcont.max:kW, lcont.max:166A

### General Information

Global Commercial Alias	ACS800-U1-0175-7
Product ID	3AUA0000015490
ABB Type Designation	ACS800-U1-0175-7
Catalog Description	ACS800-U1-0175-7; ACS800-U1-0175-7 Pcont.max:kW, lcont.max:166A

### Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS800-U1-0175-7 Pcont.max:kW, lcont.max:166A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Dimensions

Product Net Weight	67 kg
Product Net Depth / Length	399 mm
Product Net Height	880 mm
Product Net Width	300 mm

### Technical

Frame Size	R6
------------	----

### Additional Information

Product Main Type	ACS800-U1-0175-7
Product Name	Frequency Converter

**Classifications**

UNSPSC	39122001
--------	----------

**Environmental**

SCIP	9137de42-9806-4708-a144-33d9e4e244e2 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

**Categories**

Drives → Low Voltage AC Drives → Legacy AC Drives → ACS800 single drives → ACS800-U1 - Wall-mounted 6-pulse drive (US)

Drives → Services → Spares and Consumables → Parts