



PRODUCT-DETAILS

ACH550-01-290A-4+B055

ACS550-01-290A-4+B055,290A,380V,IP54

General Information

Global Commercial Alias	ACH550-01-290A-4+B055
Product ID	3AUA0000026923-E
ABB Type Designation	ACH550-01-290A-4+B055
Catalog Description	ACS550-01-290A-4+B055,290A,380V,IP54

Additional Information

ABB Type Designation	ACH550-01-290A-4+B055
CN8	85044096
Country of Origin	China (CN)
Customs Tariff Number	85044099
Frame Size	R6
Global Commercial Alias	ACH550-01-290A-4+B055
Gross Weight	98 kg
Invoice Description	ACS550-01-290A-4+B055,290A,380V,IP54
Made To Order	No
Medium Description	ACS550-01-290A-4+B055,290A,380V,IP54
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	Frequency Converter
Product Net Depth / Length	955 mm
Product Net Height	420 mm
Product Net Weight	80 kg
Product Net Width	350 mm
Product Type	ACS550___Frequency_Converter
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACS550-01-290A-4+B055,290A,380V,IP54
Stocked At (Warehouses)	Zhengzhou, China Beijing, China Shanghai, China Guang Zhou, China Singapore, Singapore Beijing, China Singapore, Singapore

	Tokyo, Japan
	Australia, Australia
Two Speed Motor	No
UNSPSC	39122001
WEEE B2C / B2B	Business To Business
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)