

PRODUCT-DETAILS

ACS320-01U-02A4-2

ACS320-01U-02A4-2, 240VAC, Pn 0.5 HP, I2LD 6.1A, IP20



General Information

Global Commercial Alias	ACS320-01U-02A4-2
Product ID	3AUA0000039639
ABB Type Designation	ACS320-01U-02A4-2
EAN	6438177222514
Catalog Description	ACS320-01U-02A4-2, 240VAC, Pn 0.5 HP, I2LD 6.1A, IP20
Long Description	The compact ACS320 will save energy throughout your pump and fan HVAC applications. From booster pumps, exhaust and condenser fans to supply and return fans, the drive's built-in HVAC features such as embedded BACnet (MS/TP) ensure easy and complete integration into building management systems.

Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044084
Invoice Description	ACS320-01U-02A4-2, 240VAC, Pn 0.5 HP, I2LD 6.1A, IP20
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	1.179 kg
Product Net Depth / Length	6.34 in
Product Net Height	9.41 in
Product Net Width	2.76 in

Technical	
Frequency (f)	50/60 Hz
Frame Size	R0
Input Voltage (U _{in})	200 ... 240 V
Ecodesign Exemption	Energy efficiency data is not provided for the 1~230 V drives. The drives with one phase input are not in the scope of the EU ecodesign requirements (Regulation EU/2019/1781).

Additional Information	
Product Name	Frequency converter

Classifications	
UNSPSC	39122001

Environmental	
SCIP	ec655904-52c0-4b46-941b-2b893a86cbf9 Finland (FI)
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACS320 - HVAC OEM pump and fan microdrive	

