



PRODUCT-DETAILS

ACS800-U31-0070-7

ACS800-U31-0070-7; ACS800-U31-0070-7

Pcont.max:75kW, Icont.max:79A

General Information

Global Commercial Alias	ACS800-U31-0070-7
Product ID	3AUA0000051530
ABB Type Designation	ACS800-U31-0070-7
Catalog Description	ACS800-U31-0070-7; ACS800-U31-0070-7 Pcont.max:75kW, Icont.max:79A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS800-U31-0070-7 Pcont.max:75kW, Icont.max:79A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	100 kg
Product Net Depth / Length	440 mm
Product Net Height	970 mm
Product Net Width	300 mm

Technical

Frame Size	R6
------------	----

Additional Information

Product Main Type	ACS800-U31-0070-7
Product Name	Frequency Converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	ad4703a4-aba8-42cb-8396-31f2b1b816b0 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Legacy AC Drives → ACS800 single drives → ACS800-U31 - Wall-mounted low harmonic drive (US)

Drives → Services → Spares and Consumables → Parts