



## PRODUCT-DETAILS

# ACS800-U31-0100-7

## ACS800-U31-0100-7; ACS800-U31-0100-7

### Pcont.max:90kW, Icont.max:93A

#### General Information

Global Commercial Alias	ACS800-U31-0100-7
Product ID	3AUA0000051531
ABB Type Designation	ACS800-U31-0100-7
Catalog Description	ACS800-U31-0100-7; ACS800-U31-0100-7 Pcont.max:90kW, Icont.max:93A

#### Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS800-U31-0100-7 Pcont.max:90kW, Icont.max:93A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

#### Dimensions

Product Net Weight	100 kg
Product Net Depth / Length	440 mm
Product Net Height	970 mm
Product Net Width	300 mm

#### Technical

Frame Size	R6
------------	----

#### Additional Information

Product Main Type	ACS800-U31-0100-7
Product Name	Frequency Converter

#### Classifications

UNSPSC		39122001
Environmental		
SCIP		ad4703a4-aba8-42cb-8396-31f2b1b816b0 Finland (FI)
WEEE Category		4. Large Equipment (Any External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → Legacy AC Drives → ACS800 single drives → ACS800-U31 - Wall-mounted low harmonic drive (US)	
Drives → Services → Spares and Consumables → Parts	