



## PRODUCT-DETAILS

# ACQ810-04-040A-4

## ACQ810-04-040A-4; ACQ810-04-040A-4

### Pcont.max:22kW, Icont.max:50A

#### General Information

Global Commercial Alias	ACQ810-04-040A-4
Product ID	3AUA0000056555
ABB Type Designation	ACQ810-04-040A-4
Catalog Description	ACQ810-04-040A-4; ACQ810-04-040A-4 Pcont.max:22kW, Icont.max:50A

#### Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACQ810-04-040A-4 Pcont.max:22kW, Icont.max:50A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

#### Dimensions

Product Net Depth / Length	298 mm
Product Net Height	567 mm
Product Net Width	166 mm

#### Technical

Frame Size	C
------------	---

#### Additional Information

Product Main Type	ACQ810-04-040A-4
Product Name	Frequency Converter

#### Classifications

UNSPSC	39122001
--------	----------

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories
Drives → Services → Spares and Consumables → Parts