



## PRODUCT-DETAILS

# ACQ810-04-080A-4

ACQ810-04-080A-4; ACQ810-04-080A-4

Pcont.max:45kW, Icont.max:94A

### General Information

Global Commercial Alias	ACQ810-04-080A-4
Product ID	3AUA0000056601
ABB Type Designation	ACQ810-04-080A-4
Catalog Description	ACQ810-04-080A-4; ACQ810-04-080A-4 Pcont.max:45kW, Icont.max:94A

### Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACQ810-04-080A-4 Pcont.max:45kW, Icont.max:94A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Dimensions

Product Net Depth / Length	298 mm
Product Net Height	567 mm
Product Net Width	221 mm

### Technical

Frame Size	D
------------	---

### Additional Information

Product Main Type	ACQ810-04-080A-4
Product Name	Frequency Converter

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories
Drives → Services → Spares and Consumables → Parts