



PRODUCT-DETAILS

ACQ810-04-240A-4

ACQ810-04-240A-4; ACQ810-04-240A-4

Pcont.max:132kW, Icont.max:260A

General Information

| | |
|-------------------------|--|
| Global Commercial Alias | ACQ810-04-240A-4 |
| Product ID | 3AUA0000056606 |
| ABB Type Designation | ACQ810-04-240A-4 |
| Catalog Description | ACQ810-04-240A-4; ACQ810-04-240A-4 Pcont.max:132kW, Icont.max:260A |

Ordering

| | |
|-------------------------|--|
| Country of Origin | Finland (FI) |
| Customs Tariff Number | 85044088 |
| Invoice Description | ACQ810-04-240A-4 Pcont.max:132kW, Icont.max:260A |
| Made To Order | Yes |
| Minimum Order Quantity | 1 piece |
| Order Multiple | 1 piece |
| Quote Only | No |
| Selling Unit of Measure | piece |

Dimensions

| | |
|----------------------------|--------|
| Product Net Depth / Length | 465 mm |
| Product Net Height | 700 mm |
| Product Net Width | 312 mm |

Technical

| | |
|------------|---|
| Frame Size | E |
|------------|---|

Additional Information

| | |
|-------------------|---------------------|
| Product Main Type | ACQ810-04-240A-4 |
| Product Name | Frequency Converter |

| Classifications | |
|-----------------|----------|
| UNSPSC | 39122001 |

| Environmental | |
|---------------|---|
| WEEE Category | 4. Large Equipment (Any External Dimension More Than 50 cm) |

| Categories |
|--|
| Drives → Services → Spares and Consumables → Parts |