



PRODUCT-DETAILS

ACQ810-04-302A-4

ACQ810-04-302A-4; ACQ810-04-302A-4

Pcont.max:kW, Icont.max:340A

General Information

Global Commercial Alias	ACQ810-04-302A-4
Product ID	3AUA0000056628
ABB Type Designation	ACQ810-04-302A-4
Catalog Description	ACQ810-04-302A-4; ACQ810-04-302A-4 Pcont.max:kW, Icont.max:340A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACQ810-04-302A-4 Pcont.max:kW, Icont.max:340A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Depth / Length	568 mm
Product Net Height	1596 mm
Product Net Width	415 mm

Technical

Frame Size	G
------------	---

Additional Information

Product Main Type	ACQ810-04-302A-4
Product Name	Frequency Converter

Classifications

UNSPSC	39122001
--------	----------

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories
Drives → Services → Spares and Consumables → Parts