

PRODUCT-DETAILS

ACS355-03U-46A2-2

ACS355-DEMOCASE w;



General Information	
Global Commercial Alias	ACS355-03U-46A2-2
Product ID	3AUA0000058211
ABB Type Designation	ACS355-03U-46A2-2
EAN	6438177223863
Catalog Description	ACS355-DEMOCASE w;
Long Description	The ACS355 drives are designed to meet the requirements of an extensive range of machinery applications in food and beverage, material handling, lifting, textile, printing, rubber and plastics, and woodworking applications. The drive is user-friendly, yet it provides a wide range of built-in technology such as the safe torque off functionality and sequence programming, reducing the need for additional control electronics. The product offers options and diverse functionality to cater to the needs set for speed and torque control of AC induction and permanent magnet motors.

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044080
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure piece

Dimensions

Product Net Weight 0 kg

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	48 ... 63 Hz
Frame Size	R4
Input Voltage (U _{in})	200 ... 240 V

Additional Information

Product Name AC Drive

Classifications

UNSPSC 39122001

Environmental

SCIP	5ccf04b1-b2ac-4a7f-9bd9-b04944c85343 Finland (FI)
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Machinery Drives → ACS355 - Machinery Drive

