



PRODUCT-DETAILS

ACSM1-04AL-03A0-4

ACSM1-04AL-03A0-4; ACSM1-04AL-03A0-4 PN:1,1kW, IN:3A

General Information

Global Commercial Alias	ACSM1-04AL-03A0-4
Product ID	3AUA0000071902
ABB Type Designation	ACSM1-04AL-03A0-4
Catalog Description	ACSM1-04AL-03A0-4; ACSM1-04AL-03A0-4 PN:1,1kW, IN:3A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044084
Invoice Description	ACSM1-04AL-03A0-4 PN:1,1kW, IN:3A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	2.8 kg
Product Net Depth / Length	146 mm
Product Net Height	364 mm
Product Net Width	90 mm

Technical

Number of Phases	3
Frequency (f)	48 ... 63 Hz
Frame Size	A
Input Voltage (U_{in})	380 ... 480 V
Mounting Type	Wall-mounted
Output Current, Normal	3 A
Use (I_n)	
Output Power, Normal	1.1 kW
Use (P_n)	

Additional Information	
Product Main Type	ACSM1-04AL-03A0-4
Product Name	Frequency Converter

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → Legacy AC Drives → ACSM1-04 - Machinery Drive Module	
Drives → Services → Spares and Consumables → Parts	