



## PRODUCT-DETAILS

# ACSM1-04CL-060A-4

## ACSM1-04CL-060A-4; ACSM1-04CL-060A-4 PN:30kW, IN:60A

### General Information

Global Commercial Alias	ACSM1-04CL-060A-4
Product ID	3AUA0000071953
ABB Type Designation	ACSM1-04CL-060A-4
Catalog Description	ACSM1-04CL-060A-4; ACSM1-04CL-060A-4 PN:30kW, IN:60A

### Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACSM1-04CL-060A-4 PN:30kW, IN:60A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Dimensions

Product Net Weight	17 kg
Product Net Depth / Length	225 mm
Product Net Height	467 mm
Product Net Width	220 mm

### Technical

Number of Phases	3
Frequency (f)	48 ... 63 Hz
Frame Size	D
Input Voltage ( $U_{in}$ )	380 ... 480 V
Mounting Type	Wall-mounted
Output Current, Normal Use ( $I_n$ )	60 A
Output Power, Normal Use ( $P_n$ )	30 kW

Additional Information	
Product Main Type	ACSM1-04CL-060A-4
Product Name	Frequency Converter

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → Legacy AC Drives → ACSM1-04 - Machinery Drive Module	
Drives → Services → Spares and Consumables → Parts	