

PRODUCT-DETAILS

ACSM1-04PL-031A-4

ACSM1-04PL-031A-4; ACSM1-04PL-031A-4

PN:15kW, IN:31A

General Information

| | |
|-------------------------|--|
| Global Commercial Alias | ACSM1-04PL-031A-4 |
| Product ID | 3AUA0000071961 |
| ABB Type Designation | ACSM1-04PL-031A-4 |
| Catalog Description | ACSM1-04PL-031A-4; ACSM1-04PL-031A-4 PN:15kW, IN:31A |

Ordering

| | |
|-------------------------|-----------------------------------|
| Country of Origin | Finland (FI) |
| Customs Tariff Number | 85044088 |
| Invoice Description | ACSM1-04PL-031A-4 PN:15kW, IN:31A |
| Made To Order | No |
| Minimum Order Quantity | 1 piece |
| Order Multiple | 1 piece |
| Quote Only | No |
| Selling Unit of Measure | piece |

Dimensions

| | |
|----------------------------|--------|
| Product Net Weight | 10 kg |
| Product Net Depth / Length | 225 mm |
| Product Net Height | 467 mm |
| Product Net Width | 165 mm |

Technical

| | |
|----------------------------------|---------------|
| Number of Phases | 3 |
| Frequency (f) | 48 ... 63 Hz |
| Frame Size | C |
| Input Voltage (U _{in}) | 380 ... 480 V |
| Mounting Type | Wall-mounted |
| Output Current, Normal | 31 A |
| Use (I _n) | |
| Output Power, Normal | 15 kW |

Use (P_n)

Additional Information

| | |
|-------------------|---------------------|
| Product Main Type | ACSM1-04PL-031A-4 |
| Product Name | Frequency Converter |

Classifications

| | |
|--------|----------|
| UNSPSC | 39122001 |
|--------|----------|

Environmental

| | |
|---------------|--|
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |
|---------------|--|

Categories

Drives → Low Voltage AC Drives → Legacy AC Drives → ACSM1-04 - Machinery Drive Module
Drives → Services → Spares and Consumables → Parts