



## PRODUCT-DETAILS

# ACSM1-04PS-040A-4

ACSM1-04PS-040A-4; ACSM1-04PS-040A-4

PN:18,5kW, IN:40A

### General Information

Global Commercial Alias	ACSM1-04PS-040A-4
Product ID	3AUA0000072009
ABB Type Designation	ACSM1-04PS-040A-4
Catalog Description	ACSM1-04PS-040A-4; ACSM1-04PS-040A-4 PN:18,5kW, IN:40A

### Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACSM1-04PS-040A-4 PN:18,5kW, IN:40A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Dimensions

Product Net Weight	10 kg
Product Net Depth / Length	225 mm
Product Net Height	467 mm
Product Net Width	165 mm

### Technical

Number of Phases	3
Frequency (f)	48 ... 63 Hz
Frame Size	C
Input Voltage (U <sub>in</sub> )	380 ... 480 V
Mounting Type	Wall-mounted
Output Current, Normal	40 A
Use (I <sub>n</sub> )	
Output Power, Normal	18.5 kW

Use (P<sub>n</sub>)

Additional Information

Product Main Type	ACSM1-04PS-040A-4
Product Name	Frequency Converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Categories

Drives → Low Voltage AC Drives → Legacy AC Drives → ACSM1-04 - Machinery Drive Module  
Drives → Services → Spares and Consumables → Parts