

PRODUCT-DETAILS

ACS580-01-05A6-4

LV AC general purpose wall-mounted drive (ACS580-01-05A6-4)



General Information

Global Commercial Alias	ACS580-01-05A6-4
Product ID	3AUA0000080489
ABB Type Designation	ACS580-01-05A6-4
EAN	6438177305453
Catalog Description	LV AC general purpose wall-mounted drive (ACS580-01-05A6-4)

Long Description	The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture.
	All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. Versatile and straightforward settings menu and assistants enable fast setup, commissioning, use and maintenance, while rugged and robust design makes it a good fit for various environments. With the ACS580 drives you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in IP21 enclosure as standard. Also, IP55 and flange mounting units are available.

Ordering

Country of Origin	China (CN) Finland (FI)
Customs Tariff Number	85044084
Invoice Description	ACS580-01-05A6-4 Pn 2,2 kW I2n 5,6 A, Protection class IP 21 (UL type 1)

	EMC class C2
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	4.8 kg
Product Net Depth / Length	345 mm
Product Net Height	468 mm
Product Net Width	228 mm

Technical

Frame Size	R0
------------	----

Additional Information

Product Main Type	ACS580
Product Name	Frequency converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive

