



PRODUCT-DETAILS

ACQ810-04-03A5-2

ACQ810-04-03A5-2; ACQ810-04-03A5-2

Pcont.max:0,55kW, Icont.max:4,8A

General Information

Global Commercial Alias	ACQ810-04-03A5-2
Product ID	3AUA0000088500
ABB Type Designation	ACQ810-04-03A5-2
Catalog Description	ACQ810-04-03A5-2; ACQ810-04-03A5-2 Pcont.max:0,55kW, Icont.max:4,8A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044084
Invoice Description	ACQ810-04-03A5-2 Pcont.max:0,55kW, Icont.max:4,8A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Depth / Length	219 mm
Product Net Height	364 mm
Product Net Width	94 mm

Technical

Frame Size	A
------------	---

Additional Information

Product Main Type	ACQ810-04-03A5-2
Product Name	Frequency Converter

Classifications

UNSPSC	39122001
--------	----------

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories
Drives → Services → Spares and Consumables → Parts