

PRODUCT-DETAILS

ACS355-DEMOCASE w/US cord  
ACS355-03U-01A2-4+B063, 480VAC, Pn  
0.5HP, I2LD 1.2A, IP66



General Information	
Global Commercial Alias	ACS355-DEMOCASE w/US cord
Product ID	3AUA0000141652
ABB Type Designation	ACS355-DEMOCASE w/US cord
EAN	6438177455882
Catalog Description	ACS355-03U-01A2-4+B063, 480VAC, Pn 0.5HP, I2LD 1.2A, IP66
Long Description	The ACS355 drives are designed to meet the requirements of an extensive range of machinery applications in food and beverage, material handling, lifting, textile, printing, rubber and plastics, and woodworking applications. The drive is user-friendly, yet it provides a wide range of built-in technology such as the safe torque off functionality and sequence programming, reducing the need for additional control electronics. The product offers options and diverse functionality to cater to the needs set for speed and torque control of AC induction and permanent magnet motors.

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044080
Invoice Description	ACS355-03U-01A2-4+B063, 480VAC, Pn 0.5HP, I2LD 1.2A, IP66
Made To Order	No

Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	17.4 lb
Product Net Depth / Length	11.06 in
Product Net Height	12 in
Product Net Width	7.68 in

Technical

Number of Phases	3
Degree of Protection	IP66
Enclosure Type NEMA	Type4X
Frequency (f)	50/60 Hz
Frame Size	R0
Input Voltage ( $U_{in}$ )	380...480 V
Mounting Type	Wall-mounting
Output Current, Normal Use ( $I_n$ )	1 A
Output Power, Light-Overload Use ( $P_{LD}$ )	0.5 Hp
Output Power, Normal Use ( $P_n$ )	0.5 Hp

Additional Information

Product Name	AC Drive
--------------	----------

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

---

## Categories

---

Drives → Low Voltage AC Drives → Machinery Drives → ACS355 - Machinery Drive

