

PRODUCT-DETAILS

ACS880-17-2530A-3

ACS880-17-2530A-3 PN:1400kW, IN:2530A



General Information

Global Commercial Alias	ACS880-17-2530A-3
Product ID	3AUA0000170258
ABB Type Designation	ACS880-17-2530A-3
Catalog Description	ACS880-17-2530A-3 PN:1400kW, IN:2530A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACS880-17-2530A-3 PN:1400kW, IN:2530A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Technical

Frame Size	nxR8i
Ecodesign Exemption	Energy efficiency data is not provided for the drive. The regenerative

drives are exempt from the EU ecodesign requirements (Regulation EU/2019/1781, §2.3.c).

Additional Information

Product Main Type	ACS880-17-2530A-3
Product Name	Frequency Converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	944D8A5E-036D-404E-9036-0D3C1EA703AD Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-17 - Cabinet-built regenerative single drive

