

## PRODUCT-DETAILS

# ACS880-17-1680A-7

ACS880-17-1680A-7 PN:1600kW, IN:1680A



### General Information

Global Commercial Alias	ACS880-17-1680A-7
Product ID	3AUA0000170302
ABB Type Designation	ACS880-17-1680A-7
Catalog Description	ACS880-17-1680A-7 PN:1600kW, IN:1680A

### Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACS880-17-1680A-7 PN:1600kW, IN:1680A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Technical

Frame Size	nxR8i
Ecodesign Exemption	Energy efficiency data is not provided for the drive. The regenerative

drives are exempt from the EU ecodesign requirements (Regulation EU/2019/1781, §2.3.c).

Additional Information

Product Main Type	ACS880-17-1680A-7
Product Name	Frequency Converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	944D8A5E-036D-404E-9036-0D3C1EA703AD Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-17 - Cabinet-built regenerative single drive

