

## PRODUCT-DETAILS

# ACS880-04XT-1160A-5

ACS880-04XT-1160A-5 Pcont.max:800kW,  
Icont.max:1160A



## General Information

Global Commercial Alias	ACS880-04XT-1160A-5
Product ID	3AUA0000182366
ABB Type Designation	ACS880-04XT-1160A-5
Catalog Description	ACS880-04XT-1160A-5 Pcont.max:800kW, Icont.max:1160A

## Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS880-04XT-1160A-5 Pcont.max:800kW, Icont.max:1160A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

## Dimensions

Product Net Weight	161 kg
Product Net Depth /	506 mm

Length	
Product Net Height	1541 mm
Product Net Width	350 mm

Technical

Frame Size	2xR10
Ecodesign Exemption	Energy efficiency data is not provided for the drive module/module package. The drive modules/module packages are not considered as VSD and are not in the scope of the EU ecodesign requirements (Regulation EU/2019/1781).

Additional Information

Product Main Type	ACS880-04XT-1160A-5
Product Name	Frequency Converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	38EAC3ED-6729-45A3-99A3-F7FA089E57C4 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 drive modules → ACS880-04XT - Single drive module package

