

PRODUCT-DETAILS

ACS880-04XT-1080A-7

ACS880-04XT-1080A-7 Pcont.max:1000kW,
Icont.max:1080A



General Information

Global Commercial Alias	ACS880-04XT-1080A-7
Product ID	3AUA0000182369
ABB Type Designation	ACS880-04XT-1080A-7
Catalog Description	ACS880-04XT-1080A-7 Pcont.max:1000kW, Icont.max:1080A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS880-04XT-1080A-7 Pcont.max:1000kW, Icont.max:1080A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	199 kg
Product Net Depth /	506 mm

Length	
Product Net Height	1741 mm
Product Net Width	350 mm

Technical

Frame Size	2xR11
Ecodesign Exemption	Energy efficiency data is not provided for the drive module/module package. The drive modules/module packages are not considered as VSD and are not in the scope of the EU ecodesign requirements (Regulation EU/2019/1781).

Additional Information

Product Main Type	ACS880-04XT-1080A-7
Product Name	Frequency Converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	38EAC3ED-6729-45A3-99A3-F7FA089E57C4 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 drive modules → ACS880-04XT - Single drive module package

