

PRODUCT-DETAILS

ACS580-01-12A6-4+B056

LV AC general purpose wall-mounted drive (ACS580-01-12A6-4+B056)



General Information

Global Commercial Alias	ACS580-01-12A6-4+B056
Product ID	3AUA0000190596
ABB Type Designation	ACS580-01-12A6-4+B056
Catalog Description	LV AC general purpose wall-mounted drive (ACS580-01-12A6-4+B056)
	The ACS580-01 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture.

Long Description	All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. Versatile and straightforward settings menu and assistants enable fast setup, commissioning, use and maintenance, while rugged and robust design makes it a good fit for various environments. With the ACS580 drives you can easily take full control of your processes to comprehensively manage your plant. The wall-mounted ACS580-01 comes in IP21 enclosure as standard. Also, IP55 and flange mounting units are available.
------------------	--

Ordering

Country of Origin	China (CN) Finland (FI)
Customs Tariff Number	85044084
Invoice Description	ACS580-01-12A6-4+B056 Pn 5,5 kW I2n 12,6 A, Protection class IP55, EMC class C2
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	5.48 kg
Product Net Depth / Length	361 mm
Product Net Height	468 mm
Product Net Width	228 mm

Technical

Degree of Protection	IP55
Frame Size	R1

Additional Information

Product Main Type	ACS580
Product Name	Frequency converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive

