

## PRODUCT-DETAILS

# ACH580-01-014A-4+B056

LV AC wall-mounted drive for HVAC, 14 A, 380 ... 480 V (ACH580-01-014A-4+B056)



## General Information

Global Commercial Alias	ACH580-01-014A-4+B056
Product ID	3AUA0000222400
ABB Type Designation	ACH580-01-014A-4+B056
EAN	6438177507833
Catalog Description	LV AC wall-mounted drive for HVAC, 14 A, 380 ... 480 V (ACH580-01-014A-4+B056)
Long Description	ACH580 HVAC drive offering has all key features built-in to control fans, pumps and compressors, and more complex equipment like air-handling units and chillers, ensuring smooth, energy-efficient operation of your HVAC systems in normal and mission-critical situations. The built-in features significantly reduce installation time and the intuitive control panel with an HVAC-specific primary settings menu and help assistants makes startup, commissioning and operation easy. The optional Bluetooth® capability enables the commissioning and monitoring of the drive from a distance. The ACH580-01 comes in IP21 enclosure and can be installed on the wall as standard. Also, IP55 and flange mounting units are available.

## Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Invoice Description	ACH580-01-014A-4+B056, 480VAC, Pn 10HP, I2LD 14A, N12/IP55
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	15 lb
Product Net Depth / Length	9.4 in
Product Net Height	21.49 in
Product Net Width	5.1 in
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
Frequency (f)	50/60 Hz
Frame Size	R2
Input Voltage ( $U_{in}$ )	440 ... 480 V
Mounting Type	Wall-mounting
Output Current, Normal Use ( $I_n$ )	14 A
Output Power, Light-Overload Use ( $P_{LD}$ )	10 Hp
Apparent Power Output	12 kV·A
Efficiency Level	IE2
Standby Loss	14 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	79 W	0.7 %	88.6 %
0 / 50 %	96 W	0.8 %	92.5 %
0 / 100 %	152 W	1.3 %	94.0 %
50 / 25 %	83 W	0.7 %	93.9 %
50 / 50 %	103 W	0.9 %	96.0 %
50 / 100 %	167 W	1.4 %	96.7 %
90 / 50 %	110 W	0.9 %	97.6 %
90 / 100 %	187 W	1.6 %	97.9 %

Temperature Rating	Maximum 40 °C
--------------------	---------------

Additional Information

Product Name	AC Drive
--------------	----------

Classifications

Environmental

WEEE Category

4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-01 - Wall-mounted drive for HVAC

