



## PRODUCT-DETAILS

# ACQ580-01-260A-4

## LV AC wall-mounted drive for water and wastewater, UL: Pld 200 Hp, 260 A, 460 V (ACQ580-01-260A-4)

### General Information

Global Commercial Alias	ACQ580-01-260A-4
Product ID	3AUA0000222424
ABB Type Designation	ACQ580-01-260A-4
EAN	6438177508076
Catalog Description	LV AC wall-mounted drive for water and wastewater, UL: Pld 200 Hp, 260 A, 460 V (ACQ580-01-260A-4)

Long Description	The ACQ580-01 drives deliver innovative pump features for the water and wastewater industry, securing energy efficient flow of water and wastewater in your pumping solutions. This robust and compact wall-mounted drive has built-in pump application functionality such as sensorless flow calculation, multipump control, level control, soft pipe fill, dry run protection, quick ramps and a solution for keeping the impeller of the pump clean. Usability is further enhanced with the intuitive Hand-Off-Auto control panel, the PC tool Drive composer and an optional Bluetooth® control panel. The built-in energy calculator visualizes the energy savings achieved with the use of the drive. The ACQ580-01 variant comes in IP21 enclosure as standard and can be installed on the wall. Also, IP55 and flange mounting units are available.
------------------	---

### Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044084
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Dimensions

Product Net Weight	152.2 lb
Product Net Depth / Length	15.47 in
Product Net Height	38.01 in
Product Net Width	11.81 in
Package Level 1 Units	1 carton

Technical	
Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	50/60 Hz
Frame Size	R8
Input Voltage (U <sub>in</sub> )	440 ... 480 V
Mounting Type	Wall-mounting
Apparent Power Output	216 kV·A
Efficiency Level	IE2
Standby Loss	61 W

Complete Drive Module  
Efficiency (61800-9-2)

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	890 W	0.4 %	93.0 %
0 / 50 %	1224 W	0.6 %	94.9 %
0 / 100 %	2160 W	1.0 %	95.4 %
50 / 25 %	980 W	0.5 %	96.2 %
50 / 50 %	1391 W	0.6 %	97.1 %
50 / 100 %	2560 W	1.2 %	97.3 %
90 / 50 %	1657 W	0.8 %	98.1 %
90 / 100 %	3398 W	1.6 %	98.0 %

Temperature Rating	Maximum 40 °C
--------------------	---------------

Additional Information	
Product Name	AC Drive

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

---

## Categories

---

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ580-01 - Wall-mounted drive for water and wastewater