



## PRODUCT-DETAILS

# ACH580-BCR-023A-4

HVAC packaged drive with e-clipse bypass and circuit breaker disconnect US, UL: Pld 15 Hp, 23 A, 460 V (ACH580-BCR-023A-4)

### General Information

Global Commercial Alias	ACH580-BCR-023A-4
Product ID	3AUA0000225663
ABB Type Designation	ACH580-BCR-023A-4
EAN	6438177515500
Catalog Description	HVAC packaged drive with e-clipse bypass and circuit breaker disconnect US, UL: Pld 15 Hp, 23 A, 460 V (ACH580-BCR-023A-4)
Long Description	<p>The ACH580 with ABB E-clipse bypass has an integrated UL (NEMA) Type 1, 12 or 3R enclosure with a bypass motor starter and is available from 1 to 350 hp at 230/460/575 V.</p> <p>The ACH580 with ABB E-clipse bypass provides an input disconnect switch or circuit breaker, both including fast acting drive fuses, with door mounted and interlocked switch (padlockable in the OFF position), a bypass starter, electronic motor overload protection, a door mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability.</p>

### Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Dimensions

Product Net Weight	84 lb
Product Net Depth / Length	13.9 in
Product Net Height	33.16 in
Product Net Width	17.63 in

### Technical

Number of Phases	3
------------------	---

Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	50/60 Hz
Frame Size	R2
Input Voltage ( $U_{in}$ )	440 ... 480 V

Additional Information	
Product Name	-

Categories
Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-BCR - HVAC packaged drive with e-clipse bypass and circuit breaker disconnect US