

PRODUCT-DETAILS

ACH580-BCR-027A-4+B058

HVAC packaged drive with e-clipse bypass and circuit breaker disconnect US, UL: Pld 20 Hp, 27 A (ACH580-BCR-027A-4+B058)



General Information

Global Commercial Alias	ACH580-BCR-027A-4+B058
Product ID	3AUA0000225670
ABB Type Designation	ACH580-BCR-027A-4+B058
EAN	6438177515579
Catalog Description	HVAC packaged drive with e-clipse bypass and circuit breaker disconnect US, UL: Pld 20 Hp, 27 A (ACH580-BCR-027A-4+B058)
Long Description	<p>The ACH580 with ABB E-Clipse bypass has an integrated UL (NEMA) Type 1, 12 or 3R enclosure with a bypass motor starter and is available from 1 to 350 hp at 230/460/575 V.</p> <p>The ACH580 with ABB E-Clipse bypass provides an input disconnect switch or circuit breaker with door mounted and interlocked switch (padlockable in the OFF position), a bypass starter, electronic motor overload protection, a door mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability</p>

Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Invoice Description	ACH580-BCR-027A-4+B058, PLD 20HP, I2LD 27A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece

Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	194 lb
Product Net Depth / Length	15.4 in
Product Net Height	40.7 in
Product Net Width	20.7 in
Package Level 1 Units	1 carton

Technical	
Number of Phases	3
Degree of Protection	IP24
Enclosure Type NEMA	Type3R
Frequency (f)	50/60 Hz
Frame Size	R3
Input Voltage (U _{in})	440 ... 480 V
Mounting Type	Cabinet-built

Additional Information	
Product Name	AC Drive

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories	
------------	--

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-BCR - HVAC packaged drive with e-clipse bypass and circuit breaker disconnect US

