



PRODUCT-DETAILS

# ACH580-BDR-034A-4+B056

## HVAC packaged drive with e-clipse bypass and disconnect US, UL: Pld 25 Hp, 34 A (ACH580-BDR-034A-4+B056)



General Information	
Global Commercial Alias	ACH580-BDR-034A-4+B056
Product ID	3AUA0000225977
ABB Type Designation	ACH580-BDR-034A-4+B056
EAN	6438177518648
Catalog Description	HVAC packaged drive with e-clipse bypass and disconnect US, UL: Pld 25 Hp, 34 A (ACH580-BDR-034A-4+B056)
Long Description	<p>The ACH580 with ABB E-Clipse bypass has an integrated UL (NEMA) Type 1, 12 or 3R enclosure with a bypass motor starter and is available from 1 to 350 hp at 230/460/575 V.</p> <p>The ACH580 with ABB E-Clipse bypass provides an input disconnect switch or circuit breaker with door mounted and interlocked switch (padlockable in the OFF position), a bypass starter, electronic motor overload protection, a door mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability</p>

Ordering	
Country of Origin	United States (US)
Customs Tariff Number	85044080
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure piece

Dimensions

Product Net Weight 0 kg

Technical

Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
Frequency (f)	50/60 Hz
Input Voltage (U <sub>in</sub> )	440 ... 480 V

Additional Information

Product Name AC Drive

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-BDR - HVAC packaged drive with e-clipse bypass and disconnect US



