

## PRODUCT-DETAILS

# ACH580-PDR-04A8-4+B056

HVAC drive with disconnect US, UL: Pld 3 Hp, 4.8 A (ACH580-PDR-04A8-4+B056)



## General Information

Global Commercial Alias	ACH580-PDR-04A8-4+B056
Product ID	3AUA0000226281
ABB Type Designation	ACH580-PDR-04A8-4+B056
Catalog Description	HVAC drive with disconnect US, UL: Pld 3 Hp, 4.8 A (ACH580-PDR-04A8-4+B056)
Long Description	The ACH580 Packaged Drive includes an ACH580 drive in a UL (NEMA) Type 1, 12 or 3R enclosure with either an input disconnect switch and fast acting fuses or an input circuit breaker. It is available from 1 to 350 hp at 230/460/575 V. The ACH580 Packaged Drive provides a door-mounted input disconnect switch (padlockable in the OFF position), electronic motor overload protection, a door-mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability

## Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece

Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	0 kg
--------------------	------

Technical

Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
Frequency (f)	50/60 Hz
Input Voltage (U <sub>in</sub> )	440 ... 480 V

Additional Information

Product Name	AC Drive
--------------	----------

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-PDR - HVAC drive with disconnect US



