

PRODUCT-DETAILS

ACH580-PDR-124A-4+B056

HVAC drive with disconnect US, UL: Pld 100 Hp, 124 A (ACH580-PDR-124A-4+B056)



General Information

Global Commercial Alias	ACH580-PDR-124A-4+B056
Product ID	3AUA0000226289
ABB Type Designation	ACH580-PDR-124A-4+B056
EAN	6438177521334
Catalog Description	HVAC drive with disconnect US, UL: Pld 100 Hp, 124 A (ACH580-PDR-124A-4+B056)
Long Description	The ACH580 Packaged Drive includes an ACH580 drive in a UL (NEMA) Type 1, 12 or 3R enclosure with either an input disconnect switch and fast acting fuses or an input circuit breaker. It is available from 1 to 350 hp at 230/460/575 V. The ACH580 Packaged Drive provides a door-mounted input disconnect switch (padlockable in the OFF position), electronic motor overload protection, a door-mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability

Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Invoice Description	ACH580-PDR-124A-4+B056, PLd 100HP, I2LD 124A
Made To Order	No

Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	359.4 lb
Product Net Depth / Length	19.04 in
Product Net Height	48.07 in
Product Net Width	28.24 in
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
Frequency (f)	50/60 Hz
Frame Size	R6
Input Voltage (U _{in})	440 ... 480 V
Mounting Type	Cabinet-built

Additional Information

Product Name	AC Drive
--------------	----------

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-PDR - HVAC drive with disconnect US

