



PRODUCT-DETAILS

ACH580-VCR-06A1-6

HVAC drive with vertical e-clipse bypass and circuit breaker disconnect US, UL: Pld 5 Hp, 6.1 A, 575 V (ACH580-VCR-06A1-6)

General Information

Global Commercial Alias	ACH580-VCR-06A1-6
Product ID	3AUA0000226905
ABB Type Designation	ACH580-VCR-06A1-6
EAN	6438177522942

Catalog Description	HVAC drive with vertical e-clipse bypass and circuit breaker disconnect US, UL: Pld 5 Hp, 6.1 A, 575 V (ACH580-VCR-06A1-6)
---------------------	--

Long Description	The ACH580 with ABB E-Clipse bypass has an integrated UL (NEMA) Type 1 enclosure with a bypass motor starter and is available from 1 to 75 hp at 230/460/575 V. The ACH580 with ABB E-Clipse bypass provides an input disconnect switch or circuit breaker, both including fast acting drive fuses, with door mounted and interlocked switch (padlockable in the OFF position), a bypass starter, electronic motor overload protection, a door mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability
------------------	--

Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	50.7 lb
Product Net Depth / Length	10.77 in
Product Net Height	44.1 in
Product Net Width	5.39 in

Technical	
Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	50/60 Hz
Frame Size	R2
Input Voltage (U _{in})	500 ... 600 V

Additional Information	
Product Name	-

Categories	
<div>Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-VCR - HVAC drive with vertical e-clipse bypass and circuit breaker disconnect US</div>	