



## PRODUCT-DETAILS

# ACH580-PDR-022A-6

HVAC drive with disconnect US, UL: Pld 20 Hp, 22 A, 575 V (ACH580-PDR-022A-6)

### General Information

Global Commercial Alias	ACH580-PDR-022A-6
Product ID	3AUA0000227379
ABB Type Designation	ACH580-PDR-022A-6
EAN	6438177527428
Catalog Description	HVAC drive with disconnect US, UL: Pld 20 Hp, 22 A, 575 V (ACH580-PDR-022A-6)
Long Description	The ACH580 Packaged Drive includes an ACH580 drive in a UL (NEMA) Type 1, 12 or 3R enclosure with input disconnect switch or circuit breaker, both including fast acting drive fuses. It is available from 1 to 350 hp at 230/460/575 V. The ACH580 Packaged Drive provides a door-mounted input disconnect switch (padlockable in the OFF position), electronic motor overload protection, a door-mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability.

### Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Dimensions

Product Net Weight	39 lb
Product Net Depth / Length	13.22 in
Product Net Height	34.86 in
Product Net Width	8.39 in

### Technical

Number of Phases	3
------------------	---

Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	50/60 Hz
Frame Size	R3
Input Voltage (U <sub>in</sub> )	500 ... 600 V

Additional Information

Product Name	-
--------------	---

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-PDR - HVAC drive with disconnect US