



## PRODUCT-DETAILS

# ACH580-VDR-075A-2

HVAC drive with vertical e-clipse bypass and circuit breaker disconnect US, UL: Pld 25 Hp, 74.8 A, 230 V (ACH580-VDR-075A-2)

### General Information

Global Commercial Alias	ACH580-VDR-075A-2
Product ID	3AUA0000227490
ABB Type Designation	ACH580-VDR-075A-2
EAN	6438177528531
Catalog Description	HVAC drive with vertical e-clipse bypass and circuit breaker disconnect US, UL: Pld 25 Hp, 74.8 A, 230 V (ACH580-VDR-075A-2)
Long Description	The ACH580 with ABB E-Clipse bypass has an integrated UL (NEMA) Type 1 enclosure with a bypass motor starter and is available from 1 to 75 hp at 230/460/575 V. The ACH580 with ABB E-Clipse bypass provides an input disconnect switch or circuit breaker, both including fast acting drive fuses, with door mounted and interlocked switch (padlockable in the OFF position), a bypass starter, electronic motor overload protection, a door mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability

### Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Dimensions

Product Net Weight	86 lb
Product Net Depth / Length	12 in
Product Net Height	56.82 in
Product Net Width	8.44 in

### Technical

Number of Phases	3
------------------	---

Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	50/60 Hz
Frame Size	R4
Input Voltage (U <sub>in</sub> )	200 ... 240 V

Additional Information

Product Name	-
--------------	---

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-VDR - HVAC drive with vertical e-clipse bypass and disconnect US