

PRODUCT-DETAILS

ACH580-BCR-059A-2+B058

HVAC packaged drive with e-clipse bypass and circuit breaker disconnect US, UL: Pld 20 Hp, 59.4 A (ACH580-BCR-059A-2+B058)



General Information

| | |
|-------------------------|--|
| Global Commercial Alias | ACH580-BCR-059A-2+B058 |
| Product ID | 3AUA0000227541 |
| ABB Type Designation | ACH580-BCR-059A-2+B058 |
| EAN | 6438177529040 |
| Catalog Description | HVAC packaged drive with e-clipse bypass and circuit breaker disconnect US, UL: Pld 20 Hp, 59.4 A (ACH580-BCR-059A-2+B058) |
| Long Description | <p>The ACH580 with ABB E-Clipse bypass has an integrated UL (NEMA) Type 1, 12 or 3R enclosure with a bypass motor starter and is available from 1 to 350 hp at 230/460/575 V.</p> <p>The ACH580 with ABB E-Clipse bypass provides an input disconnect switch or circuit breaker with door mounted and interlocked switch (padlockable in the OFF position), a bypass starter, electronic motor overload protection, a door mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability</p> |

Ordering

| | |
|------------------------|--------------------|
| Country of Origin | United States (US) |
| Customs Tariff Number | 85044080 |
| Made To Order | No |
| Minimum Order Quantity | 1 piece |
| Order Multiple | 1 piece |
| Quote Only | No |

Selling Unit of Measure piece

Dimensions

Product Net Weight 0 kg

Technical

| | |
|----------------------------------|---------------|
| Number of Phases | 3 |
| Enclosure Type NEMA | Type3R |
| Frequency (f) | 50/60 Hz |
| Input Voltage (U _{in}) | 200 ... 240 V |

Additional Information

Product Name AC Drive

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-BCR - HVAC packaged drive with e-clipse bypass and circuit breaker disconnect US



