



PRODUCT-DETAILS

ACH580-BDR-273A-2

HVAC packaged drive with e-clipse bypass and disconnect US, UL: Pld 100 Hp, 273 A, 230 V (ACH580-BDR-273A-2)

General Information	
Global Commercial Alias	ACH580-BDR-273A-2
Product ID	3AUA0000227668
ABB Type Designation	ACH580-BDR-273A-2
EAN	6438177530312
Catalog Description	HVAC packaged drive with e-clipse bypass and disconnect US, UL: Pld 100 Hp, 273 A, 230 V (ACH580-BDR-273A-2)
Long Description	<p>The ACH580 with ABB E-Clipse bypass has an integrated UL (NEMA) Type 1, 12 or 3R enclosure with a bypass motor starter and is available from 1 to 350 hp at 230/460/575 V.</p> <p>The ACH580 with ABB E-Clipse bypass provides an input disconnect switch or circuit breaker, both including fast acting drive fuses, with door mounted and interlocked switch (padlockable in the OFF position), a bypass starter, electronic motor overload protection, a door mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability.</p>

Ordering	
Country of Origin	United States (US)
Customs Tariff Number	85044080
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	0 lb
Product Net Depth / Length	0 in
Product Net Height	0 in
Product Net Width	0 in

Technical	
Number of Phases	3

Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	50/60 Hz
Frame Size	R8
Input Voltage (U _{in})	200 ... 240 V

Additional Information

Product Name	-
--------------	---

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-BDR - HVAC packaged drive with e-clipse bypass and disconnect US