

## PRODUCT-DETAILS

# ACH580-PCR-07A5-2+B056

HVAC drive with circuit breaker disconnect US,  
UL: Pld 2 Hp, 7.5 A (ACH580-PCR-07A5-  
2+B056)



## General Information

Global Commercial Alias	ACH580-PCR-07A5-2+B056
Product ID	3AUA0000227823
ABB Type Designation	ACH580-PCR-07A5-2+B056
Catalog Description	HVAC drive with circuit breaker disconnect US, UL: Pld 2 Hp, 7.5 A (ACH580-PCR-07A5-2+B056)
Long Description	The ACH580 Packaged Drive includes an ACH580 drive in a UL (NEMA) Type 1, 12 or 3R enclosure with either an input disconnect switch and fast acting fuses or an input circuit breaker. It is available from 1 to 350 hp at 230/460/575 V. The ACH580 Packaged Drive provides a door-mounted input disconnect switch (padlockable in the OFF position), electronic motor overload protection, a door-mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability

## Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	0 kg

Technical	
Number of Phases	3
Degree of Protection	IP55
Enclosure Type NEMA	Type12
Frequency (f)	50/60 Hz
Input Voltage (U <sub>in</sub> )	200 ... 240 V

Additional Information	
Product Name	AC Drive

### Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-PCR - HVAC drive with circuit breaker disconnect US



