

PRODUCT-DETAILS

ACH580-PCR-04A6-2+B058

HVAC drive with circuit breaker disconnect US, UL: Pld 5 Hp, 16.7 A (ACH580-PCR-04A6- 2+B058)



General Information	
Global Commercial Alias	ACH580-PCR-04A6-2+B058
Product ID	3AUA0000227837
ABB Type Designation	ACH580-PCR-04A6-2+B058
Catalog Description	HVAC drive with circuit breaker disconnect US, UL: Pld 5 Hp, 16.7 A (ACH580-PCR-04A6-2+B058)
Long Description	The ACH580 Packaged Drive includes an ACH580 drive in a UL (NEMA) Type 1, 12 or 3R enclosure with either an input disconnect switch and fast acting fuses or an input circuit breaker. It is available from 1 to 350 hp at 230/460/575 V. The ACH580 Packaged Drive provides a door-mounted input disconnect switch (padlockable in the OFF position), electronic motor overload protection, a door-mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability

Ordering	
Country of Origin	United States (US)
Customs Tariff Number	85044080
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece

Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	0 kg
--------------------	------

Technical

Number of Phases	3
Enclosure Type NEMA	Type3R
Frequency (f)	50/60 Hz
Input Voltage (U _{in})	200 ... 240 V

Additional Information

Product Name	AC Drive
--------------	----------

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-PCR - HVAC drive with circuit breaker disconnect US



