



## PRODUCT-DETAILS

# ACS255-03U-30A0-2+B068

LV AC micro drive, UL: Pld 10 Hp, 30 A (ACS255-03U-30A0-2+B068)

### General Information

Global Commercial Alias	ACS255-03U-30A0-2+B068
Product ID	3AUA0000232559
ABB Type Designation	ACS255-03U-30A0-2+B068
Catalog Description	LV AC micro drive, UL: Pld 10 Hp, 30 A (ACS255-03U-30A0-2+B068)
Long Description	ACS255-03U-30A0-2+B068

### Ordering

Country of Origin	United Kingdom (GB)
Customs Tariff Number	85044080
Invoice Description	ACS255-03U-30A0-2+B068
Made To Order	No
Minimum Order Quantity	1 EA
Order Multiple	1 EA
Quote Only	No
Selling Unit of Measure	each

### Dimensions

Product Net Weight	0 lb
--------------------	------

### Technical

Number of Phases	3
Degree of Protection	IP66
Enclosure Type NEMA	Type4X
Frequency (f)	0-500 Hz
Frame Size	Undefined
Input Voltage ( $U_{in}$ )	200 ... 240 V

Additional Information	
Product Name	FREQUENCY CONVERTOR

Classifications	
UNSPSC	39122001

Categories
Drives → Low Voltage AC Drives → Micro Drives → ACS255 - Micro Drive for North America