



PRODUCT-DETAILS

AYK580-01-114A-2
(AYK580-01-114A-2)



General Information	
Global Commercial Alias	AYK580-01-114A-2
Product ID	3AUA0000233139
ABB Type Designation	AYK580-01-114A-2
Catalog Description	(AYK580-01-114A-2)
Long Description	AYK580-01-114A-2

Ordering	
Country of Origin	United States (US)
Customs Tariff Number	85044080
Invoice Description	AYK580-01-114A-2
Made To Order	No
Minimum Order Quantity	1 EA
Order Multiple	1 EA
Quote Only	No
Selling Unit of Measure	each

Dimensions	
Product Net Weight	0 kg

Package Level 1 Units

1 EA

Technical

Frame Size	R5
Apparent Power Output	45 kV·A
Efficiency Level	IE2
Standby Loss	19 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	317 W	0.7 %	88.4 %
0 / 50 %	431 W	0.9 %	91.5 %
0 / 100 %	801 W	1.8 %	92.0 %
50 / 25 %	347 W	0.8 %	93.5 %
50 / 50 %	489 W	1.1 %	95.2 %
50 / 100 %	963 W	2.1 %	95.2 %
90 / 50 %	581 W	1.3 %	96.8 %
90 / 100 %	1268 W	2.8 %	96.5 %

Temperature Rating

Maximum 40 °C

Additional Information

Product Name	Frequency converter
--------------	---------------------

Classifications

UNSPSC	39122001
--------	----------

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-01 - Wall-mounted drive for HVAC

