



PRODUCT-DETAILS

AYK580-01-240A-4
(AYK580-01-240A-4)



General Information	
Global Commercial Alias	AYK580-01-240A-4
Product ID	3AUA0000233162
ABB Type Designation	AYK580-01-240A-4
Catalog Description	(AYK580-01-240A-4)
Long Description	AYK580-01-240A-4

Ordering	
Country of Origin	United States (US)
Customs Tariff Number	85044080
Invoice Description	AYK580-01-240A-4
Made To Order	No
Minimum Order Quantity	1 EA
Order Multiple	1 EA
Quote Only	No
Selling Unit of Measure	each

Dimensions	
Product Net Weight	0 kg

Package Level 1 Units

1 EA

Technical

Frame Size	R8
Apparent Power Output	200 kV·A
Efficiency Level	IE2
Standby Loss	61 W
Complete Drive Module	
Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	828 W	0.4 %	92.9 %
0 / 50 %	1129 W	0.6 %	94.9 %
0 / 100 %	1987 W	1.0 %	95.4 %
50 / 25 %	903 W	0.5 %	96.2 %
50 / 50 %	1278 W	0.6 %	97.1 %
50 / 100 %	2324 W	1.2 %	97.4 %
90 / 50 %	1502 W	0.8 %	98.1 %
90 / 100 %	3039 W	1.5 %	98.1 %

Temperature Rating

Maximum 40 °C

Additional Information

Product Name	Frequency converter
--------------	---------------------

Classifications

UNSPSC	39122001
--------	----------

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-01 - Wall-mounted drive for HVAC

