



PRODUCT-DETAILS

ACS255-01U-04A3-1+B068

LV AC micro drive, UL: Pld 1 Hp, 4.3 A (ACS255-01U-04A3-1+B068)

General Information

Global Commercial Alias	ACS255-01U-04A3-1+B068
Product ID	3AUA0000234180
ABB Type Designation	ACS255-01U-04A3-1+B068
EAN	6438177626725
Catalog Description	LV AC micro drive, UL: Pld 1 Hp, 4.3 A (ACS255-01U-04A3-1+B068)
Long Description	ACS255-01U-04A3-1+B068

Ordering

Country of Origin	United Kingdom (GB)
Customs Tariff Number	85044080
Invoice Description	ACS255-01U-04A3-1+B068
Made To Order	No
Minimum Order Quantity	1 EA
Order Multiple	1 EA
Quote Only	No
Selling Unit of Measure	each

Dimensions

Product Net Weight	0 lb
--------------------	------

Technical

Number of Phases	1
Degree of Protection	IP66
Enclosure Type NEMA	Type4X
Frequency (f)	0-500 Hz

Frame Size	F1
Input Voltage (U_{in})	110 ... 120 V

Additional Information

Product Name	FREQUENCY CONVERTOR
--------------	---------------------

Classifications

UNSPSC	39122001
--------	----------

Categories

Drives → Low Voltage AC Drives → Micro Drives → ACS255 - Micro Drive for North America