



PRODUCT-DETAILS

ACS255-03U-07A0-2+B068

LV AC micro drive, UL: Pld 2 Hp, 7 A (ACS255-03U-07A0-2+B068)

General Information

| | |
|-------------------------|---|
| Global Commercial Alias | ACS255-03U-07A0-2+B068 |
| Product ID | 3AUJA0000234204 |
| ABB Type Designation | ACS255-03U-07A0-2+B068 |
| EAN | 6438177626947 |
| Catalog Description | LV AC micro drive, UL: Pld 2 Hp, 7 A (ACS255-03U-07A0-2+B068) |
| Long Description | ACS255-03U-07A0-2+B068 |

Ordering

| | |
|-------------------------|------------------------|
| Country of Origin | United Kingdom (GB) |
| Customs Tariff Number | 85044080 |
| Invoice Description | ACS255-03U-07A0-2+B068 |
| Made To Order | No |
| Minimum Order Quantity | 1 EA |
| Order Multiple | 1 EA |
| Quote Only | No |
| Selling Unit of Measure | each |

Dimensions

| | |
|--------------------|------|
| Product Net Weight | 0 lb |
|--------------------|------|

Technical

| | |
|----------------------|----------|
| Number of Phases | 3 |
| Degree of Protection | IP66 |
| Enclosure Type NEMA | Type4X |
| Frequency (f) | 0-500 Hz |

| | |
|----------------------------|---------------|
| Frame Size | F2 |
| Input Voltage (U_{in}) | 200 ... 240 V |

Additional Information

| | |
|--------------|---------------------|
| Product Name | FREQUENCY CONVERTOR |
|--------------|---------------------|

Classifications

| | |
|--------|----------|
| UNSPSC | 39122001 |
|--------|----------|

Categories

Drives → Low Voltage AC Drives → Micro Drives → ACS255 - Micro Drive for North America