



PRODUCT-DETAILS

ACS255-03U-01A2-4+B068

LV AC micro drive, UL: Pld 0.5 Hp, 1.2 A
(ACS255-03U-01A2-4+B068)

General Information

Global Commercial Alias	ACS255-03U-01A2-4+B068
Product ID	3AUA0000234214
ABB Type Designation	ACS255-03U-01A2-4+B068
EAN	6438177627043
Catalog Description	LV AC micro drive, UL: Pld 0.5 Hp, 1.2 A (ACS255-03U-01A2-4+B068)
Long Description	ACS255-03U-01A2-4+B068

Ordering

Country of Origin	United Kingdom (GB)
Customs Tariff Number	85044080
Invoice Description	ACS255-03U-01A2-4+B068
Made To Order	No
Minimum Order Quantity	1 EA
Order Multiple	1 EA
Quote Only	No
Selling Unit of Measure	each

Dimensions

Product Net Weight	0 lb
--------------------	------

Technical

Number of Phases	3
Degree of Protection	IP66
Enclosure Type NEMA	Type4X
Frequency (f)	0-500 Hz
Frame Size	F1
Input Voltage (U_{in})	380 ... 480 V

Additional Information	
Product Name	FREQUENCY CONVERTOR

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → Micro Drives → ACS255 - Micro Drive for North America	